



#### COMMENTS

Wavetek settings:  
 100 Hz range, dial set to 0.8 - 1.1 (80 - 100 Hz)  
 sine wave, no invert, no -20 dB attenuation  
 duty cycle = "CAL"  
 null DC offset  
 pull out amplitude knob (-20 dB scale)

#### Lock-In Amplifier Settings

60 dB (1000x gain)  
 1 sec time const, 10x output switch OFF

SCALE	none	DATE	12-Jul-01, 3:17:02 PM
DRAWN BY	Pete R. Jemian, UNICAT, 2-0863		
FILENAME	zrh\F:\Visio\33BM\dcm-omega2-lockin.vsd		
PAGE	Page 1 of 1	NAME	Page-1
TITLE	<b>Proposed 33BM DCM Omega2 hardware feedback system</b>		